



# 中国国家强制性产品认证证书

证书编号: 2006010401205635

## 委托人名称、地址

领承(上海)贸易有限公司  
上海外高桥保税区华京路8号331室

## 生产者(制造商)名称、地址

伦茨传动有限公司  
Breslauer Str. 3, D-32699 Extental (Germany)

## 生产企业名称、地址

伦茨运营有限公司  
Hans Lenze Str. 1/Breslauer Str. 3, D-32699 Extental (Germany)

## 产品名称和系列、规格、型号

三相异步电动机

见附件

## 产品标准和技术要求

GB12350-2009

上述产品符合强制性产品认证实施规则  
CNCA-C04-01:2014的要求,特发此证。

发证日期: 2016年08月01日      有效期至: 2020年11月16日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书,证书首次颁发日期: 2006年10月18日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>



Q 1494896



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2006010401205635

## NAME AND ADDRESS OF THE APPLICANT

Lenze(Shanghai)Trading Co., Ltd.  
Room331, No.8, Huajing Road, Wai Gao Qiao Free Trade Zone, Shanghai

## NAME AND ADDRESS OF THE MANUFACTURER

Lenze Drives GmbH  
Breslauer Str.3, D~32699 Extental (Germany)

## NAME AND ADDRESS OF THE FACTORY

Lenze Operations GmbH  
Hans Lenze Str.1/Breslauer Str.3, D-32699 Extental (Germany)

## NAME, MODEL AND SPECIFICATION

Three-phase Asynchronous Motor

See Appendix

## THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB12350-2009

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification(REF NO. CNCA-C04-01:2014).

Date of issue: Aug.01,2016      Date of expiry: Nov.16,2020

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Oct.18,2006

This certificate can be verified through CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



President:

Wang Kejiao

**CHINA QUALITY CERTIFICATION CENTRE**

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>



Q 1494896



# 中国国家强制性产品认证证书

附录:

第 1 页 共 5 页

证书编号: 2006010401205635

纸号: 1494896

序号	型号	额定电压	额定频率	额定功率	额定转速 或极数	工作制	绝缘等级
1	SDuvwxx 047-21	$\Delta$ 230V/ Y 400V	50Hz	75W	2P	S1	F
2	SDuvwxx 047-21	$\Delta$ 230V/ Y 400V	60Hz	75W	2P	S1	F
3	SDuvwxx 047-21	$\Delta$ 230V/ Y 400V	100Hz	75W	2P	S1	F
4	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	50Hz	90W	2P	S1	F
5	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	60Hz	90W	2P	S1	F
6	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	100Hz	90W	2P	S1	F
7	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	50Hz	225W	2P	S1	F
8	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	60Hz	225W	2P	S1	F
9	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	100Hz	225W	2P	S1	F
10	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	50Hz	240W	2P	S1	F
11	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	60Hz	240W	2P	S1	F
12	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	100Hz	240W	2P	S1	F
13	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	50Hz	530W	2P	S1	F
14	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	60Hz	530W	2P	S1	F
15	SDuvwxx 056-21	$\Delta$ 230V/ Y 400V	100Hz	530W	2P	S1	F
16	SDuvwxx 063-21	$\Delta$ 230V/ Y 400V	50Hz	400W	2P	S1	F

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>





# 中国国家强制性产品认证证书

附录:

第 2 页 共 5 页

证书编号: 2006010401205635

纸号: 1494896

17	SDuvwxx 063-21	$\Delta$ 230V/ Y 400V	60Hz	400W	2P	S1	F
18	SDuvwxx 063-21	$\Delta$ 230V/ Y 400V	100Hz	400W	2P	S1	F
19	SDuvwxx 063-21	$\Delta$ 230V/ Y 400V	50Hz	500W	2P	S1	F
20	SDuvwxx 063-21	$\Delta$ 230V/ Y 400V	60Hz	500W	2P	S1	F
21	SDuvwxx 063-21	$\Delta$ 230V/ Y 400V	100Hz	500W	2P	S1	F
22	SDuvwxx 063-31	$\Delta$ 230V/ Y 400V	50Hz	600W	2P	S1	F
23	SDuvwxx 063-31	$\Delta$ 230V/ Y 400V	60Hz	600W	2P	S1	F
24	SDuvwxx 063-31	$\Delta$ 230V/ Y 400V	100Hz	600W	2P	S1	F
25	SDuvwxx 047-22	$\Delta$ 230V/ Y 400V	50Hz	75W	4P	S1	F
26	SDuvwxx 047-22	$\Delta$ 230V/ Y 400V	60Hz	75W	4P	S1	F
27	SDuvwxx 047-22	$\Delta$ 230V/ Y 400V	100Hz	75W	4P	S1	F
28	SDuvwxx 056-22	$\Delta$ 230V/ Y 400V	50Hz	120W	4P	S1	F
29	SDuvwxx 056-22	$\Delta$ 230V/ Y 400V	60Hz	120W	4P	S1	F
30	SDuvwxx 056-22	$\Delta$ 230V/ Y 400V	100Hz	120W	4P	S1	F
31	SDuvwxx 056-22	$\Delta$ 230V/ Y 400V	50Hz	135W	4P	S1	F
32	SDuvwxx 056-22	$\Delta$ 230V/ Y 400V	60Hz	135W	4P	S1	F
33	SDuvwxx 056-22	$\Delta$ 230V/ Y 400V	100Hz	135W	4P	S1	F
34	SDuvwxx 056-22	$\Delta$ 230V/ Y 400V	50Hz	240W	4P	S1	F

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>





# 中国国家强制性产品认证证书

附录:

第 3 页 共 5 页

证书编号: 2006010401205635

纸号: 1494896

35	SDUvwxx 056-22	$\Delta$ 230V/ Y 400V	60Hz	240W	4P	S1	F
36	SDUvwxx 056-22	$\Delta$ 230V/ Y 400V	100Hz	240W	4P	S1	F
37	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	50Hz	160W	4P	S1	F
38	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	60Hz	160W	4P	S1	F
39	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	100Hz	160W	4P	S1	F
40	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	50Hz	200W	4P	S1	F
41	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	60Hz	200W	4P	S1	F
42	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	100Hz	200W	4P	S1	F
43	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	50Hz	240W	4P	S1	F
44	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	60Hz	240W	4P	S1	F
45	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	100Hz	240W	4P	S1	F
46	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	50Hz	400W	4P	S1	F
47	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	60Hz	400W	4P	S1	F
48	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	100Hz	400W	4P	S1	F
49	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	50Hz	430W	4P	S1	F
50	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	60Hz	430W	4P	S1	F
51	SDUvwxx 063-22	$\Delta$ 230V/ Y 400V	100Hz	430W	4P	S1	F
52	SDUvwxx 063-32	$\Delta$ 230V/ Y 400V	50Hz	300W	4P	S1	F

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>





# 中国国家强制性产品认证证书

附录:

第 4 页 共 5 页

证书编号: 2006010401205635

纸号: 1494896

53	SDuvwxx 063-32	△230V/ Y 400V	60Hz	300W	4P	S1	F
54	SDuvwxx 063-32	△230V/ Y 400V	87Hz	500W	4P	S1	F
55	SDuvwxx 063-32	△230V/ Y 400V	100Hz	300W	4P	S1	F
56	SDuvwxx 063-32	△230V/ Y 400V	50Hz	600W	4P	S1	F
57	SDuvwxx 063-32	△230V/ Y 400V	60Hz	600W	4P	S1	F
58	SDuvwxx 063-32	△230V/ Y 400V	100Hz	600W	4P	S1	F
59	SDuvwxx 056-31	△230V/ Y 400V	50Hz	180W	2P	S1	F
60	SDuvwxx 063-21	△230V/ Y 400V	50Hz	260W	2P	S1	F

单元型号命名说明:

SD u v w xx 0yy - zx  
 1 2 3 4 5 6 7

1. S = 由伦敦生产的小驱动电机; D = 三相交流

2. 字符“u” 处代表:

F = 强制风冷; S = 自助风冷 (通过对流和发散)

E = 内部风冷 (冷却的速度一定)

3. 字符“v” 处代表: G = 圆形光滑机壳; R = 圆形带筋机壳

4. 字符“w” 处代表:

A = 异步电机; S = 同步电机

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>





# 中国国家强制性产品认证证书

附录:

第 5 页 共 5 页

证书编号: 2006010401205635

纸号: 1494896

5. 字符“xx” 处代表:

BI = 制动器和增量编码器;	BR = 制动器;
BS = 制动器和旋转变压器	BV = 预留制动器;
BX = 制动器, 预留编码器	GX = 没有制动器, 没有编码器;
IG = 增量编码器	XX = 没有刹车, 没有编码器;
RS = 旋转变压器	AG = 绝对值编码器

6. 字符“yy” 处代表:

35 = 32,5 mm;      47 = 37,5 mm;      56 = 42,5 mm;      63 = 47,5 mm

7. 字符“z” 处代表: 2= 中型;      3= 长

8. 字符“x” 处代表: 1= 2 极;      2= 4 极

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国 · 北京 · 南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

