



中国国家强制性产品认证证书

证书编号: 2014010401692417

委托人名称、地址

伦茨(上海)传动系统有限公司
上海市临港新城江山路2989号

生产者(制造商)名称、地址

伦茨(上海)传动系统有限公司
上海市临港新城江山路2989号

生产企业名称、地址

福建万达电机有限公司
福建省福安市坂中工业区兴达路239号

产品名称和系列、规格、型号

三相异步电动机

见附件

产品标准和技术要求

GB12350-2009

上述产品符合强制性产品认证实施规则
CNCA-01C-013:2007的要求,特发此证。

发证日期: 2014年05月15日

有效期至: 2018年05月15日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



Q 0938026



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2014010401692417

NAME AND ADDRESS OF THE APPLICANT

Lenze Drive Systems (Shanghai) Co., Ltd.
No. 2989, Jiangshan Road Lingang, Shanghai

NAME AND ADDRESS OF THE MANUFACTURER

Lenze Drive Systems (Shanghai) Co., Ltd.
No. 2989, Jiangshan Road Lingang, Shanghai

NAME AND ADDRESS OF THE FACTORY

WONDER ELECTRIC CO., LTD
NO. 239 XINGDA ROAD FUAN ELECTRICAL MACHINERY AND APPLIANCES ZONE FUAN
FUJIAN CHINA

NAME, MODEL AND SPECIFICATION

MS SERIES THREE PHASE ASYNCHRONOUS MOTOR

See appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB12350-2009

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification (REF NO. CNCA-01C-013:2007).

Date of issue: May. 15, 2014 Date of expiry: May. 15, 2018

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 1 页 共 4 页

证书编号: 2014010401692417

纸号: 0938026

序号	型号	额定电压	额定频率	额定功率	额定转速或极数	工作制	绝缘等级
1	MDERAXX 056-22V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	90W	4 极	S1	F
2	MDERAXX 063-12V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	120W	4 极	S1	F
3	MDERAXX 063-22V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	180W	4 极	S1	F
4	MDERAXX 063-32V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	220W	4 极	S1	F
5	MDERAXX 071-12V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	250W	4 极	S1	F
6	MDERAXX 071-22V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	370W	4 极	S1	F
7	MDERAXX 071-32V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	550W	4 极	S1	F
8	MDERAXX 080-12V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	550W	4 极	S1	F
9	MDERAXX 080-22V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	750W	4 极	S1	F
10	MDERAXX 080-32V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	1100W	4 极	S1	F
11	MDERAXX 090-12V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	1100W	4 极	S1	F

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路138号9区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

第 2 页 共 4 页

附录:

证书编号: 2014010401692417

纸号: 0938026

序号	型号	额定电压	额定频率	额定功率	额定转速 或极数	工作制	绝缘等级
12	MDERAXX 056-11V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	90W	2 极	S1	F
13	MDERAXX 056-21V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	120W	2 极	S1	F
14	MDERAXX 063-11V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	180W	2 极	S1	F
15	MDERAXX 063-21V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	250W	2 极	S1	F
16	MDERAXX 063-31V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	330W	2 极	S1	F
17	MDERAXX 071-11V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	370W	2 极	S1	F
18	MDERAXX 071-21V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	550W	2 极	S1	F
19	MDERAXX 071-31V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	750W	2 极	S1	F
20	MDERAXX 080-11V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	750W	2 极	S1	F
21	MDERAXX 080-21V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	1100W	2 极	S1	F
22	MDERAXX 080-31V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	1500W	2 极	S1	F

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 3 页 共 4 页

证书编号: 2014010401692417

纸号: 0938026

序号	型号	额定电压	额定频率	额定功率	额定转速 或极数	工作制	绝缘等级
23	MDERAXX 090-11V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	1500W	2 极	S1	F
24	MDERAXX 090-31V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	2200W	2 极	S1	F
25	MDERAXX 063-13V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	90W	6 极	S1	F
26	MDERAXX 063-23V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	120W	6 极	S1	F
27	MDERAXX 071-13V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	180W	6 极	S1	F
28	MDERAXX 071-23V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	250W	6 极	S1	F
29	MDERAXX 071-33V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	370W	6 极	S1	F
30	MDERAXX 080-13V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	370W	6 极	S1	F
31	MDERAXX 080-23V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	550W	6 极	S1	F
32	MDERAXX 080-33V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	750W	6 极	S1	F
33	MDERAXX 090-13V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz/60Hz	750W	6 极	S1	F
34	MDERAXX 071-14V13	220V/380V、 230V/400V、	50Hz、60Hz、	90W	8 极	S1	F

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 4 页 共 4 页

证书编号: 2014010401692417

纸号: 0938026

序号	型号	额定电压	额定频率	额定功率	额定转速 或极数	工作制	绝缘等级
		240V/415V	50Hz\60Hz				
35	MDERAXX 071-24V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz\60Hz	120W	8 极	S1	F
36	MDERAXX 080-14V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz\60Hz	180W	8 极	S1	F
37	MDERAXX 080-24V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz\60Hz	250W	8 极	S1	F
38	MDERAXX 090-14V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz\60Hz	370W	8 极	S1	F
39	MDERAXX 090-34V13	220V/380V、 230V/400V、 240V/415V	50Hz、60Hz、 50Hz\60Hz	550W	8 极	S1	F

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

