

# The inverter for constant motion.



The BaseLine version is the entry-level model in terms of functionality and drive behavior. Featuring an integrated keypad and everything you would expect from a modern frequency inverter suitable for universal use, the 8400 BaseLine is the ideal solution for applications such as conveyor drives, pumps, fans or ventilators.

## Highlights

- V/f control without feedback (linear or square-law)
- Sensorless vector control
- Flying restart circuit
- PID controller
- I<sup>2</sup>t motor monitoring



# 8400 BaseLine Technology – At a glance

<b>Performance data</b>	
Mains: 1 AC 230/240 V	0.33 to 3 Hp (0.25 to 2.2 kW)
Mains: 3 AC 400/480 V	0.5 - 4 Hp (0.37 to 3.0 kW)
<b>Overload current</b>	150 % (60 s) Up to 200 % (3 s)
<b>Operating conditions</b>	Operating temperature 14° F to 131° F [-10 °C to +55 °C (derating above 45 °C: 2.5 %/K)] IP20 enclosure
<b>Functions</b>	DC brake function Flying restart circuit, PID controller Sensorless vector control
<b>Interfaces</b>	Memory modules, L-force diagnostics interface CANopen optional Integrated brake chopper External 24 V supply Digital inputs / outputs (5/1), analog inputs / outputs (1/1), relay
<b>Approvals</b>	CE, UL, EAC, RoHS

