

Compact and dynamic for inverter operation.



Dynamic, inverter-optimised three-phase AC motor for variable movements.

Power range:

0.55 to 22 kW (1.53 to 59.2 Nm)

This high-efficiency powerhouse is ideally suited to: applications that require large setting ranges in conjunction with compact dimensions.

Features

- More dynamic than a conventional three-phase AC motor
- More energy-efficient than IE2
- Available in the models B3, B5, B14 (4-pole) and as geared motors (2-pole, 4-pole and 6-pole)
- Setting range during inverter operation up to 1:24 with constant torque
- Enclosure IP55
- Inverter-compatible windings as standard

Technology – Inverter-optimised MF AC motors – An overview

Specifications Inverter operation at 120 Hz

Size		063	071	080	090	100	112	132
Rated power	P [kW]	0.55	1.1	2.2	4	5.5	11	15
		0.75	1.5	3		7.5		18.5 22
Rated current	I [A]	1.8	3.2	5.3	8.5	12.9	23.5	31.2
		2.3	3.9	6.6		15.9		39 44.5
Rated torque	M [Nm]	1.53	3.01	6	10.9	14.9	29.7	40.3
		2.11	4.15	8.2		20.3		49.6 59.2
Rated speed	n [rpm]	3440	3490	3500	3480	3525	3530	3560
		3400	3450	3480		3515		3560 3550

The modular system for your application

Thanks to their flexible modular design, the three-phase AC motors are ideal for use with any application:

- Brake attachments
 - Scalable braking torques
 - Long-life design
 - Various controls
- Feedback systems
 - Resolver
 - Incremental encoder
 - Absolute value encoder
- Self-ventilated or separate blower
- Connection options
 - Plug connectors
 - Terminal box
- Various thermal sensors

Other properties

Degree of protection	
EN 60529	IP55
Energy efficiency class	
	Better than IE2
Approvals	
	cURus, EAC, CCC and UkrSepro
Temperature class	
IEC / EN 60034-1 utilisation	B
IEC / EN 60034-1 insulation system	F
Climatic conditions	
Storage temperature	-30°C to +60°C
Operating temperature	-20°C to +40°C
Connection	
Power connection	Terminal box or plug connectors
Brake connection	
Blower connection	
Feedback connection	
Colour	
	Primered Uncoated Paint in various corrosion-protection designs in accordance with RAL colours