

CERTIFICATE OF COMPLIANCE

Certificate Number E210321
Report Reference E210321-2019-05-03
Date 2020-October-17

Issued to: LENZE DRIVES GMBH
BRESLAUER STR 3
EXTERTAL32699 DE

This is to certify that representative samples of MOTORS, INVERTER DUTY
See Addendum Page for Product Designation(s).

Have been investigated by UL in accordance with the Standard(s) indicated on this Certificate.

Standard(s) for Safety: UL 1004-1, Rotating Electrical Machines – General Requirements

UL 1004-8, Inverter Duty Motors

CSA C22.2 No. 100, Motors and Generators

Additional Information: See the UL Online Certifications Directory at <https://iq.ulprospector.com> for additional information

This Certificate of Compliance does not provide authorization to apply the UL Mark. Only the UL Follow-Up Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/about/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number E210321
Report Reference E210321-2019-05-03
Date 2020-October-17

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements

Listed – Class F Insulated Inverter Duty Motor models , M55xH063, M55xH071 and M55xP (x – Any digit or letter, except “A”), followed by any digits or letters tabulated below. All models are rated for max. 600V.

Frame Size	Poles	max. V	Hz	max. A	max. kW/Hp	max. r/min	Phase	Enclosure
063	4	600	50	1.18	0.25/0.34	1500	3	Totally
			60	1.18	0.25/0.34	1800		
			87	1.2	0.45/0.61	2610		
071			50	2.34	0.55/0.74	1500		
			60	2.34	0.55/0.74	1800		
			87	2.42	1.0/1.35	2610		
080			50	2.77	0.75/1	1500		
			60	2.8	0.75/1	1800		
			87	2.82	1.35/1.82	2610		
090	50	5.51	1.5/2.02	1500				
	60	5.55	1.5/2.02	1800				
	87	5.48	2.6/3.5	2610				
100	50	10.57	3.0/4.02	1500				
	60	10.62	3.0/4.02	1800				
	87	10.42	5.2/7.0	2610				
112	50	13.54	4.0/5.37	1500				
	60	13.63	4.0/5.37	1800				
	87	14.05	7.35/9.86	2610				
132	50	25.36	7.5/10.1	1500				
	60	25.63	7.5/10.1	1800				
	87	25.36	13.1/17.57	2610				

For S3 marking on nameplate, the ratings can be higher: IN = IN(S1) x 1.4; PN = PN(S1) x 1.6.

For S6 marking on nameplate, the ratings can be higher: IN = IN(S1) x 1.4; PN = PN(S1) x 1.6.

B. Mahrenholz

Bruce Mahrenholz, Director North American Certification Program

UL LLC



Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/about/locations/>